


TECHNICAL FILE - SEAT RANGER 28 MODEL

RANGER 28 model chassis is designed for usage for both four-cycle and two-cycle applications for cadet aged drivers


STANDARD SEAT

COMPKART ES (extra Soft) size - XXS, XS , 1



TOOLS REQUIRED

- Drill
- 8mm Drill Bit
- 5mm Allen Key
- 13mm Wrench
- Seat Jig



Regardless of seat size and type - 16cm is the recommended as the base setting for all applications. Increasing the measurement from 16cm will increase the weight distribution the front of the chassis, thus increasing front-end positivity and reducing rear-end balance and braking stability. We do not recommend to installing external seat stays.

For better driver fitment we provide the following items in our catalogue:

Adjustable Pedal Box | PN: C.10.15721.00

Steering Spacer Inclined | PN: C.20.12348.00-NE

Race Dept. Tip 01



We recommend using specialized Compkart seat mounting washers. Available in both 2mm and 5mm thickness.

2mm | PN: C.J32X51.NE | .BL

5mm | PN: C.J3C5X51.NE | .BL

